



1 d ₁	2 d ₂	3 Länge l				d ₃	b	h	t min.
25	M 6	16	20	25	-	8	8	10	7
30	M 6	16	20	25	-	10	10	12	7
30	M 8	16	20	25	32	10	10	12	9
36	M 8	16	20	25	32	12	12	14,5	9
36	M 10	20	30	40	-	12	12	14,5	7

Ausführung

- Kopf
 - Edelstahl (Sinterstahl)
 - nichtrostend, 1.4404
 - matt gestrahlt
- Schraube
 - Edelstahl
 - nichtrostend, 1.4301
 - matt gestrahlt
 - eingeschraubt und mit Querstift gesichert
- *Edelstahl-Eigenschaften* → Seite 2166
- RoHS

Hinweis

- siehe auch...
- *Edelstahl-Flügelmuttern GN 834* → Seite 618
 - *Edelstahl-Flügelerschrauben GN 835* → Seite 619

Bestellbeispiel (Innengewinde)

GN 432-25-M6

1 d₁
2 d₂

Bestellbeispiel (Schraube)

GN 431-25-M6-20

1 d₁
2 d₂
3 Länge l

