



- 1 Type**
- SKN** With wing knob
 - STN** With T-handle

2 Latch distance A

6	10	14	18	20	22	24	26	28
---	----	----	----	----	----	----	----	----

Specification

- Lock housing / Operating Elements **A4**
Stainless Steel AISI 316
- Latch arm
Stainless Steel AISI 316
- Other parts
Stainless Steel AISI 316
- Protection class IP 65
- IP Protection Classes → Page 2153
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Protective Guide Plates GN 120.2
→ Page 1270
- Internal Cabinet Handles GN 120.3
→ Page XYZ
- Sheet Metal Punches GN 123 → Page 1267

Information

Latches GN 115 are locked by a rotation limited to 90°, which moves the latch arm into the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Thanks to the stainless steel material, the latches are optimally suited for use in highly corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (Steel, Zinc Plated, with Operating Elements) → Page 1200
- Latches GN 115 (Stainless Steel, with Operating Elements) → Page XYZ
- Latches GN 115 (Stainless Steel, Operation with Socket Keys, Protection Classe IP 69k) → Page XYZ
- Latches GN 115 (Stainless Steel, Lockable) → Page 1208

<p>How to order</p> <p>GN 115-SG-18-NI</p>	1 Type
	2 Latch arm distance A
	3 Material