



1

2

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.
14	M 5	7	34	25
23	M 6	14	60	17
23	M 8	14	60	22
26	M 8	16	70	25
26	M 10	16	70	25
30	M 10	16	65	26
30	M 12	16	65	26
35	M 12	22	85	25
35	M 16	22	85	25

### Specification

Plastic, phenolic resin (PF)

- Operating temperature up to 110 °C
- Black, shiny finish

RoHS

When using elliptical shaped knobs GN 201, it must be ensured that the threaded stud is not too short. Otherwise, there is a risk that the duroplast plastic body could break under certain loads.

### Technical Information

Plastic Characteristics

Page

QVX

How to order

GN 201-30-M10

1 d<sub>1</sub>

2 d<sub>2</sub>