



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> Length l ±0,25	d <sub>2</sub>	h
8	30	12	26
10	40	15	31

**Specification**

**GN 224.1**

**Steel**

- Chrome plated
- Location disks
- Zinc die casting, nickel plated

CR

**GN 224.5**

**Stainless steel AISI 304**

- Matte, shot blasted
- Location disks
- Stainless Steel AISI 303

RoHS

**see also...**

**GN 224.3** Finger Handles (Plastic) Page

QVX

**Technical Information**

Stainless Steel Characteristics QVX

How to order (Steel)

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**GN 224.1-8-30-CR**

- |   |                |
|---|----------------|
| 1 | d <sub>1</sub> |
| 2 | Length l       |
| 3 | Material       |

How to order (Stainless steel)

<sup>1</sup> <sup>2</sup>  
**GN 224.5-10-40**

- |   |                |
|---|----------------|
| 1 | d <sub>1</sub> |
| 2 | Length l       |