



<b>d</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub> ≈</b>	<b>h ≈</b>
10	64 ±0,25	75	35
10	96 ±0,25	111	35
10	128 ±0,25	146	35
10	160 ±0,25	181	35
10	192 ±0,35	219	35

**Specification**

**GN 424.1**

**Steel**

Plastic coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- **SW**
- **SR**

**GN 424.5**

**Stainless steel** AISI 303

Matt brushed

RoHS

see also...

Page

**GN 565.4** Arch Handles (Aluminum, Mounting from the Back or Operator's Side) QVX

**Technical Information**

Load Rating Information

QVX

Stainless Steel Characteristics

QVX

How to order (Steel)

**GN 424.1-10-160-SR**

- 1 d
- 2 l<sub>1</sub>
- 3 Color

How to order (Stainless steel)

**GN 424.5-10-128**

- 1 d
- 2 l<sub>1</sub>