



d ₁	Length l						d ₂	d ₃	h ₁	h ₂	r	t min.
	55*	64	88*	96	100	200						
8	55*	64	88*	96	100	M 4	12	40	30	9	8	
10	88*	100	120*	180*	200	M 5	15	47	35	11	12	
12	125	160	200	250	-	M 6	-	60	44	12	12	

* suitable for 19" rack and enclosure layout

Specification

Handle

- Steel
- Powder coated
 - Black, RAL 9005, textured finish
 - Chrome plated
 - Blackened

- SW
- CR
- BT

Location disks

- Zinc die casting
- Nickel plated

RoHS

Cabinet U-Handles GN 425.1 are manufactured from a bent steel profile. Cabinet U-handles with Ø d₁ = 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

The stainless steel version is preferred over the chrome-plated version in steel for outdoor applications.

see also...	Page
GN 425.1 Cabinet U-Handles (Stainless Steel / Aluminum)	QVX
GN 425 Cabinet U-Handles (Steel, Not Angled)	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
---	-----

How to order

GN 425.1-10-100-CR

1	d ₁
2	Length l
3	Finish