



d ₁			Length l						d ₂	d ₃	h ₁	h ₂	r	t min.
NI	A4	AL	55*	64	88*	96	100	M 4	12	40	30	9	8	
8	-	8	88*	100	120*	180*	200	M 5	15	47	35	11	12	
12	-	12	125	160	200	250	-	M 6	-	60	44	12	12	

* suitable for 19" rack and enclosure layout

Specification

Stainless steel	NI	
AISI 303 for d ₁ = 8, 10		
AISI 304 for d ₁ = 12		
• Matte shot-blasted finish	GS	
• Electropolished	EP	
• Location disks for d ₁ = 8, 10		
Stainless steel AISI 303		
Stainless steel AISI 316L	A4	
• Matte shot-blasted finish	GS	
• Location disks		
Stainless Steel AISI 316L		
Aluminum	AL	
• Plastic coated		
- Black, RAL 9005, textured finish	● SW	
- Silver, RAL 9006, textured finish	● SR	
- Red, RAL 3000, textured finish	● RS	
• Anodized, natural color	● EL	
• Location disks for d ₁ = 8, 10		
Zinc die casting, nickel plated		

RoHS

Cabinet U-handles GN 425.1 are manufactured from a bent stainless steel or aluminum profile. Cabinet U-handles with Ø d₁ = 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed. The stainless steel version is preferred over the chrome-plated version in steel for outdoor applications.

see also...

	Page
GN 425.1 Cabinet U-Handles (Steel)	QVX
GN 425 Cabinet U-Handles (Aluminum / Stainless Steel, Not Angled)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order (Aluminum)

1	Material
2	d ₁
3	Length l
4	Finish

1 2 3 4
GN 425.1-AL-12-125-EL

How to order (Stainless steel)

1	Finish
2	d ₁
3	Length l
4	Finish

1 2 3 4
GN 425.1-NI-10-180-GS