



<div>1</div> <div>2</div> <div>3</div> <div>d₁</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₁</div>	Wall thickness Nominal size	<div>1</div> <div>2</div> <div>3</div> <div>s</div>	<div>1</div> <div>2</div> <div>3</div> <div>a</div> <div>Profile cross-section</div>	<div>1</div> <div>2</div> <div>3</div> <div>b</div>	<div>1</div> <div>2</div> <div>3</div> <div>d₂</div>	<div>1</div> <div>2</div> <div>3</div> <div>d₃</div>	<div>1</div> <div>2</div> <div>3</div> <div>d₄</div>	<div>1</div> <div>2</div> <div>3</div> <div>h₁</div>	<div>1</div> <div>2</div> <div>3</div> <div>h₂</div>	<div>1</div> <div>2</div> <div>3</div> <div>h₃</div>	<div>1</div> <div>2</div> <div>3</div> <div>h₄</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₂</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₃</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₄</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₅</div>	<div>1</div> <div>2</div> <div>3</div> <div>l₆</div>	<div>1</div> <div>2</div> <div>3</div> <div>m₁</div>	<div>1</div> <div>2</div> <div>3</div> <div>m₂</div>
59	15	A 1	1...10	30	44	57	50	5,1	33	25	3,5	23	28	5	34	8	19,5	30	6,3
59	20	A 1	1...10	40	44	57	50	5,1	33	25	3,5	23	28	5	34	8	19,5	30	6,3

Specification

Front body

Plastic, Polyacetal (POM)

• Operating temperature -20 °C to +60 °C

• UV resistant

Housing / Snap element

Plastic, Polyamide (PA)

• Glass fiber reinforced

• Operating temperature -20 °C to +60 °C

• UV resistant

Color

Black, matte finish

● SW

Self-tapping screws ISO 7049-ST3.5x19

Stainless steel

RoHS

Snap latches GN 449.4 combine the function of a gripping tray with that of a snap latch to provide an easy way to keep doors and covers closed.

The mounting hole must be created according to the dimensions specified in the mounting information. For mounting, first insert the front body into the hole in the door, then push in the housing from the opposite side. Use the two supplied self-tapping screws to join the housing with the front body. Finally, orient the snap element based on the reference marks and mount it on the frame or profile.

see also...

GN 449.5 Snap Latches (Stainless Steel)

QVX

GN 449.1 Spring-Bolt Door Latches (Adjustable)

QVX

Technical Information

Plastic Characteristics

QVX

How to order	1	d ₁
	2	l ₁
	3	Nominal size
	4	Color
GN 449.4-59-15-A1-SW		