



ROSTFREI

Rostfrei

Inox
Stainless
Steel

b

3

Type

N

Without increased torque

B

With increased torque

1	2									
n	d					b	h ₁	h ₂	Length l	
	Steel				Stainless steel					
6	M 4	-	-	-	M 4	-	11,5	3	1	5,9
8	M 4	M 5	M 6	-	M 6	-	16,5	4,5	1,5	8
10	M 4	M 5	M 6	M 8	M 6	M 8	19,4	5,7	3	9,8

Specification		4
Steel		SZ
Zinc plated, blue passivated		
Stainless steel		NB
Plain finish		
RoHS		

T-slot nuts GN 51b fasten attachments and accessories in the slot of aluminum profiles. They are inserted into the slot of the aluminum profile at any position and affixed by a 90° turn.

With type B, the increased torque in the nut thread ensures that the required 90° turn during installation or removal of the bolt is always reliably transmitted and the T-slot nut is aligned crosswise or lengthwise to the slot. The connection is conductive.

see also...	Page
GN 10b Aluminum Profiles (Profile Type Light)	QVX
GN 10b Aluminum Profiles (Profile Type Heavy)	QVX

How to order	
1	n
2	d
3	Type
4	Material / Finish

GN 51b-10M8-B-SZ