



elesa
Original design VCHT.

3 Type

- E With cover cap (threaded blind bore)
- D Without cover cap (thread through hole)

d ₁	d ₂ Type E	d ₃ Type D	d ₄	d ₅	h ₁	h ₂	t
32	M 5 M 6	M 5 M 6	12	10	22,5	8,5	16,5
40	M 6 M 8	M 6 M 8	14	12	27	10	20
50	M 8 M 10	M 8 M 10	18	15	30	10	20
63	M 10 M 12	M 10 M 12	20	19	35,5	14	29
74	M 12 M 16	M 12 M 16	25	17	39,5	15	29

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Bushing

Steel, zinc plated

Cover cap for type E

- Plastic, polypropylen (PP)
- Black, RAL 9005, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- DSW
- DOR
- DGR
- DGB
- DBL
- DRT
- DGN

RoHS

Star knobs GN 5337.1 with protruding bushing have important advantages: The contact surface of the bushing is exactly perpendicular to the bore and the entire diameter is made of steel. The protruding steel bushing allows a perfect cross-pin connection.

see also...

	Page
GN 5337.2 Star Knobs (Bushing Brass / Steel)	QVX
GN 5337.6 Star Knobs	QVX
GN 5337.7 Star Knobs (Bushing Stainless Steel)	QVX

Technical Information

Plastic Characteristics

QVX

How to order (Without cover cap)

GN 5337.1-40-M8-D

1	d ₁
2	d ₃
3	Type

How to order (With cover cap)

GN 5337.1-32-M5-E-DSW

1	d ₁
2	d ₂
3	Type
4	Color of the cover cap