



Rostfrei Inox
Stainless
Steel

3 Type

- E** With cover cap (threaded blind bore)
- D** Without cover cap (threaded bore)

d₁	d₂ Type E		d₃ Type D		d₄	d₅	h₁	h₂	t
25*	M 4	-	-	-	13	8	19	8	10
32	M 5	M 6	M 5	M 6	15	10	23	10	12
40	M 6	M 8	M 6	M 8	17	13	27	12	18
50	M 8	M 10	M 8	M 10	19	15	32	14	20
63	M 10	M 12	M 10	M 12	22	19	37	16	26
74	M 12	-	M 12	-	26	17	43,5	22	26
84	M 16	-	M 16	-	28	17	44	21	25

* only available in black

Specification

- Plastic
Technopolymer (Polypropylen PP)
 - Reinforced, shock resistant
 - Temperature resistant up to 90 °C
 - Black, matte finish

- Bushing
Stainless steel AISI 303

- Color of the cover cap (matte finish):

- Black, RAL 7021 ● -
- Orange, RAL 2004 ● DOR
- Gray, RAL 7035 ● DGR
- Yellow, RAL 1021 ● DGB
- Blue, RAL 5024 ● DBL
- Red, RAL 3000 ● DRT
- Green, RAL 6017 ● DGN

- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166

- RoHS

4 Information

Characteristic of the star knobs GN 5337.7 is the 5 lobes. They not only give the knobs a specific style but this shape has also enabled the operator to achieve a higher torque.

see also...

- *Star Knobs 5337.2 (Bushing Brass / Steel)* → Page 560
- *Star Knobs GN 5337 (Duroplast)* → Page 556
- *Star Knobs GN 5337.4 (Bushing Stainless Steel)* → Page 564
- *Softline Star Knobs GN 5337.6 (Bushing)* → Page 566
- *Star Knobs GN 5337.7 with Loss Protection GN 111.7* → Page 2084

How to order (Cover cap black)	1 d ₁
GN 5337.7-50-M10-E	2 d ₂ (d ₃)
	3 Type

How to order (Cover cap colored)	1 d ₁
GN 5337.7-74-M12-E-DRT	2 d ₂
	3 Type
	4 Color of the cover cap