



1 d₁	2 d₂	3 Length l					d ₃	h ₁	h ₂ ≈
25	M 5	10	16	-	-	-	12	20	10
32	M 6	10	16	20	25	30	14	23	11,5
40	M 8	20	25	30	40	-	16	27	13,5
50	M 10	20	25	30	40	55	19	30	15
60	M 12	30	40	50	-	-	22,5	34	18

Specification

- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, matte
- Threaded stud
Stainless steel AISI 304
 - Plastic Characteristics → Page 2158
 - Stainless Steel Characteristics → Page 2166
- RoHS

On request

- With threaded stud steel, zinc plated

Information

The underside of the GN 5342 is not recessed, which meets the requirements of a „hygienic“ version.

see also...

- Star Knobs with Threaded Stud GN 5337.4
(Technopolymer, Threaded Stud Stainless Steel) → Page 565
- Star Knobs GN 5337.4 with Loss Protection GN 111.7 → Page 2084

How to order		1	d ₁
GN 5342-50-M10-30		2	d ₂
		3	Length l