



1		2	3					
l ₁		d	l ₂			h ₁	h ₂	s
Nominal dimension	Actual dimension							Square
40	41	M 5	16	20	-	28	18,5	13
40	41	M 6	20	25	-	28	18,5	13
55	56,5	M 6	20	25	-	33	21,5	15
55	56,5	M 8	20	25	-	33	21,5	15
67	68,5	M 8	20	25	30	37	24,5	16,5
67	68,5	M 10	20	30	-	37	24,5	16,5
80	82	M 10	20	30	-	41,5	25	20
93	94	M 12	30	-	-	46	28,5	21

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber re-inforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Screw

- Steel
- Zinc plated, blue passivated

RoHS

T-handle screws GN 563.1 can be used on operating levers as well as on clamping fixtures. These handles lend themselves ideally for very high manual clamping forces.

see also...

	Page
GN 563.2 T-Handles (Aluminum)	QVX
GN 563 T-Handles (Plastic)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

GN 563.1-55-M8-20

1	l ₁
2	d
3	l ₂