



ROSTFREI  
Inox  
Stainless  
Steel

- 3 Type**
- A** Mounting from the back (threaded blind bore)
  - B** Mounting from the operator's side

<b>1</b> <b>b</b>		<b>2</b> <b>l<sub>1</sub></b>	<b>a</b>	<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>h<sub>1</sub> ≈</b>	<b>h<sub>2</sub></b>	<b>l<sub>2</sub> ≈</b>	<b>t<sub>1</sub> min.</b>	<b>t<sub>2</sub></b>
<b>GN 565.4</b>	<b>GN 565.9</b>									
20	20	160	13	M 6	5,3	50	5	185	8	5
20	20	192	13	M 6	5,3	50	5	221	8	5
26	-	160	17	M 8	6,4	57	6	190	11	6
26	-	192	17	M 8	6,4	57	6	227	11	6

**Specification**

- GN 565.4**
- Aluminum**
- Powder coated
    - Black, RAL 9005, textured finish
    - Red, RAL 3000, textured finish
    - Silver, RAL 9006, textured finish
  - Anodized, natural color
  - Plain finish, tumbled
- SW**  
 **RS**  
 **SR**  
 **EL**  
 **BL**
- 
- GN 565.9**
- Stainless steel** AISI 304
- Matte shot-blasted finish **MT**
- RoHS

**see also...**

	Page
<b>GN 665</b> Arch Handles (Aluminum, ellipse profile)	QVX
<b>GN 424.1</b> Arch Handles (Steel, Ø 10)	QVX
<b>GN 424.5</b> Arch Handles (Stainless Steel, Ø 10)	QVX

**Technical Information**

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order (Aluminum)

<b>1</b> <b>b</b>
<b>2</b> <b>l<sub>1</sub></b>
<b>3</b> <b>Type</b>
<b>4</b> <b>Finish</b>

**GN 565.4-20-160-B-RS**

How to order (Stainless Steel)

<b>1</b> <b>b</b>
<b>2</b> <b>l<sub>1</sub></b>
<b>3</b> <b>Type</b>
<b>4</b> <b>Finish</b>

**GN 565.9-20-192-A-MT**