



1.1

1.2

1.3

1.4

d₁	d₂	Length l			d₃	b	h₁	h₂
40	M 5	16	20	-	13,5	6	20	4
40	M 6	20	30	-	13,5	6	20	4
40	M 8	20	30	40	13,5	6	20	4
48	M 6	20	30	-	13,5	7	24	5,5
48	M 8	20	30	40	13,5	7	24	5,5
55	M 8	20	30	40	16	8	28	6,5
63	M 10	20	30	-	19	9	32	7,5
70	M 10	20	30	40	20	10	36	8

2.1

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, matte similar to RAL 7021

- Threaded stud
Stainless steel AISI 303

- Color of the cover cap (matte finish):
Black-gray, RAL 7021
Orange, RAL 2004
Gray, RAL 7035
Yellow, RAL 1021
Blue, RAL 5024
Red, RAL 3000
Green, RAL 6017



- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Design and handling of the wing screws GN 633.1 comply with the requirements and claims of the Ergostyle® product family.

see also...

- Product Family Ergostyle® → Page 18
- Wing Screws GN 639 (Small Type) → Page 613
- Wing Nuts GN 634 → Page 606
- Stainless Steel Wing Screws GN 835 → Page 619
- Wing Screws GN 633 / GN 633.1 with Loss Protection GN 111.7 → Page 2084

2.2

2.3

2.4

How to order

1	d₁
2	d₂
3	Length l
4	Color of the cover cap

GN 633.1-48-M6-20-DSG

