



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l			d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
45	M 8	20	30	-	21	26	10
45	M 10	20	30	40	21	26	10
56	M 8	20	30	40	26,5	29	11
56	M 10	20	30	40	26,5	29	11
56	M 12	30	40	50	26,5	29	11
70	M 10	30	40	50	32,5	35	13
70	M 12	30	40	50	32,5	35	13

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 130 °C
  - Black-gray, similar to RAL 7021, matte

- Star knob upper part (matte finish):
  - Black-gray, RAL 7021
  - Orange, RAL 2004
  - Gray, RAL 7035
  - Yellow, RAL 1021
  - Blue, RAL 5024
  - Red, RAL 3000
  - Green, RAL 6017

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

- Star knob upper part and lower part ultrasonically welded
- Threaded stud
  - Steel
  - Zinc plated, blue passivated

• *Plastic Characteristics* → Page 2158

• RoHS



**Information**

The design of the star knobs GN 636.4 matches the product family Ergostyle®.

see also...

- *Product Family Ergostyle®* → Page 18

How to order

<sup>1</sup>	d <sub>1</sub>
<sup>2</sup>	d <sub>2</sub>
<sup>3</sup>	Length l
<sup>4</sup>	Color upper part

**GN 636.4-56-M10-30-DSG**

