




Original design M.643 FM



Length l	a	b	d	h₁	h₂	t
86 ±0,5	14	23	5,4	44	15	5,5
117 ±0,5	16	25	6,4	49	15	6
132 ±1	16	26	6,4	53	15	8,5
179 ±1	16	27	6,4	57	15	6

Specification

Handle

Plastic, Polypropylene (PP)

- Shock resistant
- Operating temperature -20 °C to +100 °C
- Black, matte finish

Bushing

Brass

RoHS

Due to their elliptical profile, cabinet U-handles GN 725.1 are very ergonomic.

see also...

GN 565.1 Cabinet U-Handles (Aluminum)

Page

QVX

GN 565.5 Cabinet U-Handles

(Stainless Steel, Mounting from the Back or the Operator's Side)

QVX

Technical Information

Strength Properties

QVX

Plastic Characteristics

QVX

How to order

GN 725.1-179
1 Length **l**