


**Examples of application**



Latches GN 119

Latches GN 115



d <sub>1</sub>	b	h <sub>1</sub>	h <sub>2</sub>	Length l	s	useable for * d <sub>2</sub>	GN 115	GN 115.8	GN 115.9	GN 119 Edelstahl	GN 119 Stahl	GN 315.1	GN 515	GN 516	GN 516.1	GN 516.5
							31	2	6	18	35	20,5	28	x	x	x
32	2	8	18	36	20,5	30 / 32	-	-	-	-	x	x	x	x	x	x

\* Used for latches actuated by key / socket key

**Specification**

- Plastic (Polyamide PA)  
Black, matte finish
- *Plastic Characteristics* → Page 2158
- RoHS



**Information**

Opening handles GN 120.1 are simple operating elements which are used in combination with key or push-button actuated locking devices. They have a low installation height and can be mounted as required in a 90° grid pattern together with the lock housing.

Please note: The clamping range A1 ... A9 and/or the latch distance A is reduced by the dimension b.

see also...

- *List of Latch Types* → Page 1196 ff.
- *Protective Guide Plates GN 120.2* → Page 1270
- *Internal Cabinet Handles GN 120.3* → Page XYZ

**How to order**

**GN 120.1-31-SW**

1 d<sub>1</sub>

2 Color

