

- 2 Type**
- SL** With lock, lockable by turning left (different locks)
 - SR** With lock, lockable by turning right (different locks)
 - OS** Without lock, turns 90° in both directions

1

3

l_1	Latch arm distance A		d_1	d_2	h_1	h_2
67	10	18	32	20	35	25
85	10	18	37	23	41	25

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black-gray, matte, similar to RAL 7021
- Latch arm
Sheet steel zinc plated
- Key
Brass nickel plated
- Other parts
Steel zinc plated resp. brass or stainless steel
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- Same lock
- Different locks, with general key

Information

Latches GN 623.1 lock by a turning operation limited to 90°, which moves the latch arm in the locked position behind the door frame.

Latch arms with different bend angles cover a latch arm distance A from 10 and 18 mm.

The latches with lock are supplied with 2 keys. The key can be removed in both end positions.

For parts that take different locks, 400 different lock variants are available with correspondingly numbered keys.

see also...

- *Product Family Ergostyle®* → Page 18
- *List of Latch Types* → Page 1196 ff.
- *Latches GN 115 (Lockable)* → Page 1203
- *Latches GN 115 (Operation with Operating Elements)* → Page 1200



How to order

GN623.1-85-SL-18

1	l_1
2	Type
3	Latch arm distance A





Construction and assembly instructions




Konstruktionsbeispiele


mit Montagescheibe



Montagescheibe



Aufnahmebohrung
direkt eingearbeitet
(ohne Montagescheibe)



3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

