

**elesa**  
Original design EBP.FLX



**2 Type**


**B** Mounting from the operator's side

**Application example**



**Calculation drilling distance m**

l <sub>1</sub>	m
117	0.044 x D + 81.5
150	0.056 x D + 102.8



**1**

l <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	s	A/F	t
117 ±0,5	26	8,5	39	18	143	91	9	13	8,5
150 ±1	28	8,5	45	18	178	122	10	13	14

**Specification**

**Handle**

Plastic, Polypropylene (PP) with thermoplastic Elastomer (TPE)  
 • Operating temperature 0 °C to +80 °C  
 • Black-gray, matte, similar RAL 7021

**Bushing**

Brass

**Cover cap**

- Plastic, Polyamide (PA)  
 • Black-gray, RAL 7021, matte finish  
 • Orange, RAL 2004, matte finish  
 • Gray, RAL 7035, matte finish  
 • Yellow, RAL 1021, matte finish  
 • Blue, RAL 5024, matte finish  
 • Red, RAL 3000, matte finish  
 • Green, RAL 6017, matte finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

**3**

Cabinet U-handles GN 628.3 are manufactured out of a flexible plastic material. They were developed for easy assembly on arched surfaces. They cover the section from Ø 300 up to Ø 600. For Ø bigger than 600, the standard version GN 628 can be used.

The design of the cabinet U-handles GN 628.3 matches the Ergostyle® product family.

The cover caps are supplied loose.

**see also...**

	Page
<b>GN 628</b> Cabinet U-Handles (Mounting from the Back or the Operator's Side)	QVX

**Technical Information**

Product Family Ergostyle®	QVX
Strength Properties	QVX
Plastic Characteristics	QVX

**How to order**

**GN 628.3-150-B-DSG**

<b>1</b>	l <sub>1</sub>
<b>2</b>	Type
<b>3</b>	Color of the cover cap