


Application examples



- 3 Type**
- F Shackle
- L Angle piece



Buffer GN 352

**4 Identification no.**

- 1 With bore for countersunk screws DIN 7991
- 2 With bore without countersunk

b	l <sub>1</sub> Type F	l <sub>2</sub> Type L	l <sub>3</sub>	m	d	s
20	40	20	10	20	5,2	3
30	60	30	15	30	6,3	4
40	80	40	20	40	8,3	5
45	90	45	22,5	45	8,3	5

Specification

- Sheet steel
- Zinc plated, blue passivated **ZB**
- Powder coated
- Black, RAL 9005, textured finish ● **SW**
- Silver, RAL 9006, textured finish ○ **SR**
- RoHS

Information

Angle pieces and shackles GN 967 are preferably used in connection with profile systems. Square connections or connections with same contact area can so be realised in the smallest of spaces and with a high degree of stability.

Over and above the profile system configurations, the angle pieces and shackles can also be used for a wide variety of different fixing and retaining tasks, for instance in the design of jigs and fixtures.

In the version with identification no. 2, the bores are designed without countersunk hole to allow fixing with socket cap screws, nuts or rivets.

see also...

- *Product Family Standard Parts for Profile Systems* → Page 18
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order (Shackle)	1 b
	2 l <sub>1</sub>
	3 Type
<b>GN967-40-80-F-1-SW</b>	4 Identification no.
	5 Finish

How to order (Angle)	1 b
	2 l <sub>2</sub>
	3 Type
<b>GN967-30-30-L-1-SW</b>	4 Identification no.
	5 Finish