



d_1	Drehbereich	Rundlauf-toleranz	Planlauf-toleranz	max. Eingangs-drehmoment M_D in Nm	max. Belastbarkeit des Drehtellers ohne Klemmung in Nm	mit Klemmung M_K in Nm	F max. in N
55	0°... ∞	±0,02	±0,02	1,5	5	10	50
80	0°... ∞	±0,03	±0,03	2,5	5	10	100

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

