



elesa
Original design PW12

Type

- R Digits ascending clockwise
L Digits ascending anti-clockwise

d ₁	Counter	Indication after one spindle revolution	Corresponds to thread pitch	Scale		d ₂	d ₃	l ₁	l ₂
				Number of graduations	Indication precision of the pointer				
60	0000.2	000002	0,2	20	0,01	68,5	67	33	26
60	0000.5	000005	0,5	50	0,01	68,5	67	33	26
60	0001.0	000010	1,0	100	0,01	68,5	67	33	26
60	0002.0	000020	2,0	40	0,05	68,5	67	33	26
60	0002.5	000025	2,5	50	0,05	68,5	67	33	26
60	0003.0	000030	3,0	60	0,05	68,5	67	33	26
60	0004.0	000040	4,0	80	0,05	68,5	67	33	26
60	0005.0	000050	5,0	100	0,05	68,5	67	33	26

Specification

Housing

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Black, matte finish

Sight glass

- Plastic, Polyamide (PA-T)
- Clear glass, ageing proof
- Shock-resistant

Housing / Sight glass

- Operating temperature 0 °C to +100 °C
- Oil and solvent proof (not suitable for alcohol)

Pointer

- Plastic, red

Scale

- Aluminum
- Matte anodized
- Graduations black

Counter

- Digits white
- Pre-decimal positions highlighted black
- Decimal positions highlighted red

Protection class IP 65

RoHS

On request

- Special scales

Position indicators GN 000.13 have been shaped for installation into different operating elements.

The salient features of these counters are:

The housing, the hand spindle, and safety glass are produced from one single piece of material and ultrasonically welded to give a spray water proof and corrosion free unit (Protection class IP 65).

The installation principle with the forced drive allows the use of the positioning indicator GN 000.13 in any position even in case of strong vibration.

One complete revolution of the red pointer corresponds to one revolution of the spindle. This gives a very accurate reading and, combined with the digital indication from the counter, it is very simple to read.

see also...

GN 000.9 Position Indicators QVX

Technical Information

Further instructions for position indicators GN 000.13	QVX
IP Protection classes	QVX
Plastic Characteristics	QVX

Accessory

GN 534.9 Hand Knobs	QVX
GN 577.9 Handwheels	QVX
GN 323.9 Disk Handwheels	QVX

How to order

1	d ₁
2	Counter
3	Type

GN 000.13-60-0001.0-R