


- 1** Type
- SC** With key (same lock)
- SU** With key (different lock)
- 3** Identification no.
- 1** Operation, in drawn position, at the top left
- 2** Operation, in drawn position, at the top right

Type **SC / SU**



2

Latch arm distance A																					
4	6	8	10	13	14	16	18	20	22	24	26	28	30	32	34	36	38	40	42	45	50

Specification

- Front frame
Zinc die casting
Powder coated
Black, RAL 9005, textured finish ● **SW**
Silver, RAL 9006, textured finish ● **SR**
- Tray
Plastic
- Black gray (for SW)
- Light gray (for SR)
- Other parts
Steel
Zinc plated, blue passivated
- Key
Nickel silver with plastic hand piece
- **RoHS**

Accessory

- Protective Guide Plates GN 120.2
→ Page XYZ

4

Information

Latches with gripping tray GN 115.10 are used in applications which require a moulded recess in addition to the latching mechanism, e.g. if operating elements are not allowed to protrude for reasons of space. A rotary movement limited to 90° moves the latch behind the frame, with the run-up bevels at the latch making it easier to close the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

The latches are delivered with 2 keys and loosely enclosed hook. The key can be removed in both end positions.

Types with a standard lock allow every lock to be opened with the same key. For the types with different lock, there are more than 200 different lock variants, whose keys are marked by numbers.

see also...

- *Construction and Assembly Instructions* → Page 1225
- *List of Latch Types* → Page 1196 ff.
- *Latches with Gripping Tray GN 115.10 (not Lockable)* → Page 1224
- *Latches with Cabinet U-Handles GN 115.7* → Page 1222

How to order	1	2	3	4
	Type	Latch arm distance A	Identification no.	Finish
GN 115.10-SC-20-1-SR				