


3 Type

F With fixed handle

1**2**

No.	d ₁ H7 Bore	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂ ≈	Length l
100	B 7	13	16	18	10	13	31	25
101	B 8	15	19	20	13	17	40	28
102	B 8	16	20	22	14	17	45	34
103	B 10	18	23	25	16	19,5	50	41
104	B 12	20	26	28	18	21,5	56	50

Specification
Body

Steel

- Turned
- Zinc plated, blue passivated

Fixed Handle DIN 39

Steel

Zinc plated, blue passivated

RoHS

Tri-ball handles GN 10 allow fine adjustment.

An alternative in modern design are cranked handles GN 510 and control handles GN 112.1.

see also...
GN 510 Cranked Handles (Plastic) **Page**
QVX
GN 112.1 Control Handles (Zinc die casting) QVX
Technical Information

ISO Fundamental Tolerances

QVX

How to order
GN 10-104-B12-F
1 No.**2** d₁**3** Type