



1.1

1.2

1.3

1.4

1

2

$l_1$	$d$ H7 Blind bore		$b$	$h_1$	$h_2$	$h_3 \approx$	$l_2$	$t$ min.	$\varnothing$ Handle
70	S 8	-	17	19	11,5	42,5	26,5	12	18
80	S 8	-	18	21	12,5	52,5	31	12	21
90	S 10	-	19	23	13,5	52,5	35,5	15	21
100	S 10	S 12	20	25	14	67,5	40	17	23

2.1

2.2

**Specification**

**Body**

- Zinc die casting
- Powder coated
- Black, textured finish

**Revolving handle GN 598**

- Plastic, Polypropylen (PP)
- Black, matte finish
- Spindle steel
- Zinc plated, blue passivated

RoHS

Control handles GN 112.1 allow fine adjustment.

They are connected to a shaft by means of a cross pin. To simplify the installation there is a centred drilling on both sides.

**see also...**

**GN 510** Cranked Handles (Plastic) **Page**  
QVX

**Technical Information**

ISO Fundamental Tolerances QVX

2.3

2.4

**How to order**

**GN 112.1-90-S10**

1  $l_1$

2  $d$

