




- 4 Type
- D Straight lever
- E Angled lever

123										d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	l ₂
32	M 8	12	16	20	25	32	40	50	-	13,5	8	20	20,5	1,5	12,5	36	4	100
36	M 10	16	20	25	32	40	50	63	80	16	10	25	24,5	2	15	45	4,5	120
40	M 12	25	32	40	50	63	80	-	-	19	12	30	30	4	19	53	4,5	130
45	M 16	32	40	50	63	80	-	-	-	23	12	32	35,5	4	24	64	5	145

Specification

Hub / Shaft
Stainless steel AISI 303
Matte shot-blasted
Cover
Plastic, polyvinyl chloride (PVC-U)
Light gray
Ball knobs DIN 319
Plastic, phenolic resin (PF)
Black, shiny finish
Safety circlip
Plastic, polyacetal (POM)
RoHS

The overall height of flat adjustable tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...	Page
GN 126.1 Flat Adjustable Tension Levers (Zinc Die Casting, Insert Stainless Steel)	QVX
GN 125 Flat Adjustable Tension Levers (Steel)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

1234

GN 125.5-32-M8-20-D

1	d ₁
2	d ₂
3	l ₁
4	Type