






Type A  
without seals



Type B  
with seals



**Rost** **fret** **Inox**  
Stainless  
Steel

**3 Type**

- A Without seals
- B With seals

**4 Identification no.**

- 4 With 2 stainless steel cap nuts DIN 917

**1**

**2**

<b>d<sub>1</sub></b> Bore	<b>d<sub>2</sub></b> Bore	<b>b</b>	<b>d<sub>3</sub></b>	<b>k</b> Clamping length	<b>l<sub>1</sub></b>	<b>m</b>	<b>z</b> Screw locations	<b>Accessory</b> Recom. hand lever GN 911.3 for <b>z</b> <b>l<sub>2</sub></b>	
B 30	B 30	22	37	40	104	33	M 8	63	78
B 40	B 40	28	50,3	56	133	45	M 10	78	92
B 50	B 50	30	60	65	150	53	M 10	78	92

**Specification**

- Stainless steel AISI CF-8  
Matte shot-blasted
- Carriage bolt DIN 603  
Stainless steel
- Cap nuts DIN 917 / washers  
Stainless steel
- Seals
  - Sealing disks  
Plastic (Polyacetal POM)
  - Spacer ring  
Silicon, 40 ... 60 Shore A
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Adjustable Hand Levers GN 911.3  
→ Page 1785

**Information**

The clamping bores of two-way connector clamps GN 132.5 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations **z**, carriage bolts and cap nuts reduce the bore cross-section for clamping. Type B is equipped with seals at the screw locations.

For clamping without tools, the cap nuts can be replaced by adjustable hand levers GN 911.3 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → Page 1835

**How to order**

<b>1</b>	<b>d<sub>1</sub></b>
<b>2</b>	<b>d<sub>2</sub></b>
<b>3</b>	<b>Type</b>
<b>4</b>	<b>Identification no.</b>

**GN 132.5-B30-B30-A-4**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9