


- 3 Type
- B With collar
- S With countersunk head



1	2												
d ₁	d ₂	d ₃	d ₄	d ₅	d ₆	l ₁ ≈	l ₂	l ₃	A/F	t ₁	t ₂	t ₃	
5 ^{+0,10 -0,02}	M 12	16	18	9,4	6,5	16,5	21	2	4	10	1,5	17,5	
6 ^{+0,10 -0,02}	M 14	18	20	11,4	8,2	17,5	23	2	5	10	2,5	18,5	
8 ^{+0,10 -0,02}	M 16	20	22	13	11,1	19,5	25	3	6	10	3	20,5	
10 ^{+0,15 -0,05}	M 20	25	27	16,4	13,4	21,5	28	3	8	10	4	22	
12 ^{+0,15 -0,05}	M 24	30	32	19,6	15,4	29,5	39	4	10	20	5	33,5	
16 ^{+0,15 -0,05}	M 30	36	38	25	20,3	33,5	43	4	10	20	7	36,5	

Specification	4
Stainless steel AISI 303	NI
RoHS	
Technical Information	Page
List of Lock Pin Types	QVX
Stainless Steel Characteristics	QVX

Holding bushings GN 1140 are designed for ball lock pins, such as GN 113.3, or locking pins GN 114.2. They are used when the existing wall thickness is thin or for installation in a blind hole. They also provide reinforcement when the locking pin or ball lock pin is used with soft, sensitive materials. Type B establishes a defined screw-in depth due to the collar. Type S with countersunk head allows for centered, flush installation in an easily created hole.

The holding bushings fit the following locking pins and ball lock pins: GN 113.3, GN 113.4, GN 113.5, GN 113.6, GN 113.7, GN 113.8, GN 113.9, GN 113.10, GN 113.11, GN 113.12, GN 113.30, GN 114.2, GN 114.3, GN 114.6, GN 124.2, GN 124.3, GN 214.2, GN 214.3, GN 214.6

How to order	1 d ₁
	2 d ₂
	3 Type
	4 Material
GN 1140-10-M20-S-NI	