

- 1 Type**
- DK** With triangular spindle
 - VK7** With square spindle
 - VK8** With square spindle
 - SCH** With slot
 - VDE** With double bit


- 3 Identification no.**
- 1** Operation, in drawn position, at the top left
 - 2** Operation, in drawn position, at the top right

Type **DK**

Type **VK7 / VK8**

Type **SCH**

Type **VDE**



2

Latch arm distance **A**

4	6	8	10	13	14	16	18	20	22	24	26	28	30	32	34	36	38	40	42	45	50
---	---	---	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----

Specification

- Front frame
 - Zinc die casting
 - Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
- Tray
 - Plastic
 - Black gray (for SW)
 - Light gray (for SR)
- Lock housing
 - Zinc die casting
 - Powder coated, black (for SW)
 - Chrome-plated (for SR)
- Other parts
 - Steel
 - Zinc plated, blue passivated

- **SW**
- **SR**

• **RoHS**

Accessory

- Socket keys GN 119.2 → Page 1266
- Protective Guide Plates GN 120.2 → Page XYZ

Information

Latches with gripping tray GN 115.10 are used in applications which require a moulded recess in addition to the latching mechanism, e.g. if operating elements are not allowed to protrude for reasons of space.

They lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

Latches with gripping tray GN 115.10 are supplied with loosely enclosed latch arm.

see also...

- List of Latch Types → Page 1196 ff.
- Latches with Cabinet U-Handles GN 115.7 → Page 1222
- Latches with Gripping Tray GN 115.10 (Lockable) → Page 1226
- Ledge Handles with Lock GN 932 → Page 1260

How to order

GN 115.10-SCH-20-2-SR

1	Type
2	Latch arm distance A
3	Identification no.
4	Finish