



Mounting holes - outer slide



l_1	a_1	a_2
500	64	192
600	80	240
700	96	288
800	112	336

Mounting holes - inner slide



l_1	i_1	i_2
500	64	192
600	80	240
700	96	288
800	112	336

Fastening screws

For the said loading forces F_S to be absorbed reliably in the surrounding structure, all available countersunk holes of the outer and inner slide must be used. Failure to use fastening screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - standard		Outer slide	Inner slide
Countersunk screw, Phillips	DIN 965	M 5	M 4
Countersunk screw, Phillips	DIN 7997	Size 5	Size 4 / 4,5

