



Mounting holes - outer slide



l_1	a_3	a_4	a_5	a_6
400	288	320	-	-
450	288	320	-	-
500	352	384	-	-
550	352	384	-	-
600	448	480	-	-
700	448	480	-	-
800	384	416	672	704
900	416	448	768	800
1000	480	512	864	896
1200	576	608	1056	1088

Mounting holes - inner slide



l_1	i_1	i_2	i_3	i_4	i_5	i_6
400	43	118	193	268	343	-
450	43	130,5	218	305,5	393	-
500	43	143	243	343	443	-
550	43	155,5	268	380,5	493	-
600	43	168	293	418	543	-
700	43	193	343	493	643	-
800	20	271	522,5	774	-	-
900	20	305	589	874	-	-
1000	20	258,5	497	735,5	974	-
1200	20	251	482	712	943	1174

Fastening screws

For the said loading forces F_S to be absorbed reliably in the surrounding structure, all available countersunk holes of the outer and inner slide must be used. Failure to use fastening screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - standard		Outer slide	Inner slide
Countersunk screw, Phillips	DIN 965	M 5	M 4
Countersunk screw, Phillips	DIN 7997	Size 5	Size 4 / 4,5

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

