



- 3 Type
- D

 Straight lever
- E

 Angled lever

1			2									
d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	Length l	t min.
32	M 6	M 8	13,5	8	20	20,5	1,5	12,5	36	4	100	11
36	M 8	M 10	16	10	25	24,5	2	15	45	4,5	120	14
40	M 10	M 12	19	12	30	30	4	19	53	4,5	130	17
45	M 12	M 16	23	12	32	35,5	4	24	64	5	145	22

Specification

Hub / Shaft

Stainless steel AISI 303

Matte shot-blasted

Cover

Plastic, polyvinyl chloride (PVC-U)

Light gray

Ball knobs DIN 319

Plastic, phenolic resin (PF)

Black, shiny finish

Safety circlip

Plastic, polyacetal (POM)

RoHS

On request

• With threaded through hole

The overall height of flat adjustable tension levers GN 125.5 is reduced to a minimum.

As all other adjustable levers, they are ideal whenever parts have to be clamped in a confined space, or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and the lever can be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

GN 126.1 Flat Adjustable Tension Levers (Zinc Die Casting, Bushing Stainless Steel)

QVX

GN 125 Flat Adjustable Tension Levers (Steel)

QVX

Technical Information

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order

1

2

3

GN 125.5-40-M12-E

1

2

3

d₁

d₂

Type