



elesa
Original design MLP

¹ l ₁	² d ₁	² d ₂	b ₁	b ₂	b ₃	h ₁	h ₂	l ₂	l ₃	t ₁	t ₂
120	M 4	B 4,5	22	19,5	8	21	18	142	107	10	13

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black-gray, RAL 7021, matte finish ● SG

Threaded bushing

Brass

RoHS

Ledge handles GN 130.2 with bore hole B 4,5 are intended for fixing with self-tapping screws of thread size ST 4,8 such as pan head self-tapping screws DIN ISO 7049. They offer the advantage of a narrow design.

see also...

	Page
GN 130 Ledge Handles	QVX
GN 730 Ledge Handles (Aluminum)	QVX
GN 430 Ledge Handles (Aluminum)	QVX

Technical Information

Strength Properties	QVX
Plastic Characteristics	QVX

How to order

GN 130.2-120-M4-SG

¹	l ₁
²	d ₁ (d ₂)
³	Color