



elesa
Original design RE.G5

3 Bearing type

K Ball bearing

4 Type

A Wheel without bracket

1 d ₁ Wheel Ø	2 b	d ₂	Recommended ergonomic max. load in N	Max. static load capacity in N	Max. dynamic load capacity in N
80	70	20	3900	7000	5600
80	90	20	4300	9000	7000
82	70	20	4000	7000	5600
82	90	20	4400	9000	7000
82	100	20	4600	10000	8000
85	40	20	2500	4000	3500
85	70	20	4100	7000	5600
85	90	20	4500	9000	7000
85	100	20	4750	10000	8000

Specification

Wheel tread

- Plastic, polyurethane (PUR)
- Yellow
- Cast
- Hardness 92 Shore A

Wheel core

Steel

Operating temperature -20 °C to +80 °C

RoHS

Pallet truck rollers GN 22868 are used in industry and logistics for moving heavy loads.

The wheel tread is characterized by high elasticity and good wear and tear resistance.

The low wear on the ball bearing increases the service life.

see also...

	Page
GN 22885 Wheels (Wheel Core Aluminum)	QVX
GN 22886 Wheels (Wheel Core Aluminum)	QVX
GN 22887 Wheels (Wheel Core Cast Iron)	QVX

Technical Information

Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX
Plastic Characteristics	QVX

How to order

1 d ₁
2 b
3 Bearing type
4 Type

GN 22868-82-100-K-A

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

