



elesa

Original design RE.C7

2 Bearing type

G Friction bearing

3 Type

A Wheel without bracket



| d ₁ Wheel Ø | b ₁ | b ₂ | d ₂ | l ₁ | l ₂ | s | A/F | Max. dynamic load capacity in N |
|---------------------------|----------------|----------------|----------------|----------------|----------------|---|-----|---------------------------------------|
| 40 | 18 | 22 | M 6 | 32 | 4 | 2 | 10 | 300 |
| 50 | 18 | 22 | M 6 | 32 | 4 | 2 | 10 | 350 |
| 60 | 24 | 30 | M 6 | 40 | 4 | 2 | 10 | 500 |
| 80 | 24 | 30 | M 6 | 40 | 4 | 2 | 10 | 550 |

Specification**Wheel tread**

Natural rubber (NR)

- Gray
- Abrasion-resistant
- Hardness 80 Shore A

Wheel core

Plastic, polypropylene (PP)

Thread guard

- Plastic, polyamide (PA) for d₁ = 40
- Steel for d₁ > 40

Bearing pins / Nuts

Steel, zinc plated

Operating temperature -5 °C to +40 °C

RoHS

Wheels GN 22870 are used in industrial and public indoor areas for moving light materials and equipment, for example.

The wheel tread offers low rolling resistance and high elasticity. It is gentle on floors and good at overcoming obstacles.

The integrated thread guard prevents textile threads from wrapping around the wheel axle and protects the bearing from soiling.

see also...

| | Page |
|--|------|
| GN 22870 Light Duty Casters (with Bracket, Light Version) | QVX |
| GN 22870 Light Duty Casters (with Bracket, Double Wheel Version) | QVX |
| GN 22872 Wheels (Wheel Tread Thermoplastic Elastomer) | QVX |
| GN 22880 Wheels (Wheel Tread Polyurethane, Wheel Core Polyamide) | QVX |

Technical Information

| | |
|--|-----|
| Operating Conditions of Wheels and Casters | QVX |
| Technical Information for Wheels and Casters | QVX |
| Plastic Characteristics | QVX |

How to order

GN 22870-50-G-A

| | |
|---|----------------|
| 1 | d ₁ |
| 2 | Bearing type |
| 3 | Type |