



3 Type

- A** Connector plug at the top
- B** Connector plug from the bottom
- C** Connector plug at the back, (with 0,2 m cable)
- AK** Connector cable at the top
- BK** Connector cable from the bottom
- CK** Connector cable at the back

1		2													
l_1		l_2	l_3	l_4	l_5		l_6	h_1	h_2	m_1	m_2	m_3			
Small hinge wing	Broad hinge wing				Small hinge wing	Broad hinge wing	Cable length in meter Type AK / BK / CK					Small hinge wing	Broad hinge wing		
49	79	101	30	81	15	30	2 5	12	22,5	71	17	27	50		

Specification

- Zinc die casting
Powder coated
Silver metallic
- Pin
Stainless steel AISI 303
- [Load Rating Information → Page 2121](#)
- [Stainless Steel Characteristics → Page 2166](#)
- **RoHS**

Accessory

- Cable with connector coupling → [Page 1412](#)
8-pin, 5 and/or 10 meter long:
- GN 330-M12x1-8-G-5
- GN 330-M12x1-8-G-10
- Mounting plates GN 139.3 / GN 139.4
→ [Page 1402](#)

On request

- Hinges with operation angle > 0°
- Hinges with other contact terminations

Information

Hinges GN 139.1 with integrated safety switches have been designed for monitoring doors and covers of machines and plants. Opening the door will activate the switch contacts which, in turn, will then e.g. interrupt a protective circuit via break contact (NC) and at the same time signal the door opening by closing a normally open contact element (NO). The contact blocks are fitted with positive opening slow-action contacts, i.e. they will definitely be separated when activated and have no hysteresis. The angle at which the switching points are reached are adjustable (see contact travel diagram).

Together with the integrated contact blocks, the hinges are a compact, easy to mount unit with an attractive design. The mounting from the back make the hinge more tamper-proof.

Hinges **GN 139.2** without switching function act as additional hinges e.g. for larger doors or gates where several hinges are required.

How to order (With switch)	
1	l_1
2	l_2
3	Type
4	l_6
GN 139.1-49-101-AK- 5	

How to order (Without switch)	
1	l_1
2	l_2
GN 139.2-79-101	

Mechanical features				
Maximum load Information with safety factor	Load direction			
	Examples of calculation → see operating instruction	$I_1 = 49$ $I_1 = 79$	1500 N 750 N	1000 N 500 N
Fixing	from the back, 7 x threads M5, 6 mm deep			
Recommended torque	5 Nm (Screws M5)			
Protection class	IP67 / IP69K (Mind the cable conduit!)	acc. to EN 60529		
Switching principle, contact opening	Slow-action contacts force-fitted, with positive opening	acc. to IEC 60947-5-1, K		
Contact material	Silver alloy			
Operating travel diagram (scheme)	The switching points are adjustable up to 4° in direction of 0°. see operating instruction			
Maximum operating frequency	600 operating cycles / hour	acc. to IEC 60947-5-1, one operating cycle includes one opening and one closing action		
Mechanical life span	10 ⁶ operating cycles			
Actuating speed	min. 2° / second, max. 90° / second			

Electrical features / Safety features		
Utilization category	AC 15: 24 V AC / 2A / DC 13: 24 V DC / 2A (connector plug) AC 15: 250 V AC / 4A / DC 13: 250 V DC / 0,3 A (cable)	acc. to EN 60947-5-1
Contacts, termination 8-pole connector M12 or cable with 2 m or 5 m length		
Pin and cable assignment	1 - green-yellow 3 - black 5 - red 7 - brown 4 - black-white 6 - red-white 8 - blue	
Type of cable	7x0,5 mm ² , jacket PVC H05VV-F	acc. to IEC 60332-1-2 et seqq.
Short-circuit current	1000 A	acc. to EN 60947-5-1
Rated insulation voltage	30 V AC / 36 V DC (connector plug) / 250 V AC (cable)	
Short-circuit protection	2 A, 500 V, Typ gG (connector plug) / 6 A, 500 V, Typ gG (cable)	
Ambient temperature	- 25 °C up to + 80 °C	
Degree of pollution, external	3	acc. to EN 60947-5-1
Mission time (T_M)	20 years	acc. to EN ISO 13849-1
Number of cycles (B10 d)	5 000 000	acc. to EN 61820-2

Approvals, Conformities, Applicability		
Low-voltage switchgear and controlgear CE declaration IMQ: CA02.03746 UL: E 131787		EN 60947-1/2007 EN 60947-1-5 : 2004 + A1/2009
Safety applications	up to SIL 3 / PL e	acc. to EN ISO 13849-1

Other important details and hints are given in the operating instruction for GN 139.1 hinges which are included with every hinge and which are also available as PDF downloads from „www.ganternorm.com“ under „Service“.

The hinges with safety switch must be mounted and commissioned by qualified technical personnel in compliance with the details given in the operating instructions and with the national and international rules and regulations and the applicable standards. Otto Ganter GmbH & Co. KG will assume no statutory liability for missing or incorrect information and for any consequences arising therefrom.