



elesa
Original design RE.F8-WH

- 2

Bearing type
- K Ball bearing
- 3

Type (bracket)
- B Rigid bracket
- L Swivel bracket with mounting plate
- LF Swivel bracket with mounting plate, with total lock brake
- 4

Coding
- H Heavy version

d ₁ Wheel Ø	b	d ₂	h	l ₁	l ₂	l ₃	m ₁		m ₂	m ₃	r	Max. dynamic load capacity in N
							Type B	Type L / LF				
125	45	11	182	135	110	51	80	73	87	105	157	6500
150	45	11	210	135	110	60	80	73	87	105	157	7500
200	50	11	252	135	110	70	80	73	87	105	157	9000

Specification

Wheel tread / Wheel core

Plastic, polyamide (PA)

• Single part

• White

• Hardness 70 Shore D

Bracket

Welded steel design, zinc plated

ST

Swivel head bracket

• Ball thrust / Tapered roller bearing, grease-lubricated

• Relubrication possible

Operating temperature

-30 °C to +80 °C

RoHS	
see also...	Page
GN 22892 Wheels (without Bracket)	QVX
GN 22892 Medium Duty Casters (Light Version)	QVX
GN 22892 Medium Duty Casters (Light Version, with Leveling Foot)	QVX
GN 22892 Medium Duty Casters (Medium Version)	QVX

Technical Information	
Operating Conditions of Wheels and Casters	QVX
Technical Information for Wheels and Casters	QVX

How to order

1

d₁

2

Bearing type

3

Type (bracket)

4

Coding

5

Material (bracket)

1

2

3

4

5

GN 22892-150-K-B-H-ST