




2		3																			
I ₁		I ₂	d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ + 0,5	I ₃		I ₄		I ₅	m ₁	m ₂	m ₃	m ₄			
	Elongated on one side									Elongated on both sides	ZD	NI	ZD						NI		
63	-	50	M 6	6,3	6	11,5	6	6,5	13	18,5	21	31,5	34	12	43	30	15	28			
-	76	50	M 6	6,3	6	11,5	6	6,5	13	31,5	34	31,5	34	12	56	30	28	28			
90	-	60	M 8	8,4	8	15	8	8,5	17	21,5	26	51,5	56	14	63	36	18	45			
-	120	60	M 8	8,4	8	15	8	8,5	17	51,5	56	51,5	56	14	90	36	45	45			

Specification		1	5
• Zinc die casting Powder coated Black, RAL 9005, textured finish Silver, RAL 9006, textured finish	ZD		
		● SW	● SR
• Stainless steel AISI CF-8 (only type A) Matte shot blasted	NI		
			GS
• Pin			
- Stainless steel AISI 303 for ZD			
- Stainless steel AISI 316L for NI			
• Threaded stud (type C) Stainless steel AISI 316			
• Load Rating Information → Page 2121			
• Stainless Steel Characteristics → Page 2166			
• RoHS			

Information	
Hinges GN 237 with horizontally elongated hinge wings are made in a compact and sturdy design. They are used when larger spacings are required for the attachment bore holes.	
see also	
• List of Hinge Types → Page 1284 ff.	
• Plates with Tapped Holes GN 2372 (Stainless Steel) → Page 1351	
• Spacer Plates GN 2370 (Stainless Steel) → Page 1350	
• Rubber Bumper Stops GN 2374 → Page 1298	

How to order		1	Material
		2	I1
		3	I2
		4	Type
		5	Finish
GN 237-ZD-76-50-A-SR			