




d Bore	s Square	k Clamping length	l ₁	l ₂	l ₃	z Screw locations	Accessory	
							Recom. hand lever GN 911 for z l ₄	
B 20	V 20	50	68	46	48	M8-35	63	78
B 25	V 25	50	68	46	48	M8-35	63	78
B 30	V 30	50	68	46	48	M8-35	63	78
B 30	V 30	60	79	59	58	M8-50	63	78
B 32	-	60	79	59	58	M8-50	63	78
B 35	V 35	60	79	59	58	M8-50	63	78
B 40	V 40	60	79	59	58	M8-50	63	78
B 40	V 40	76	98	70	73	M10-60	78	92
B 42	-	76	98	70	73	M10-60	78	92
B 45	V 45	76	98	70	73	M10-60	78	92
B 48	-	76	98	70	73	M10-60	78	92
B 50	V 50	76	98	70	73	M10-60	78	92
B 60	V 60	90	108,5	84	83	M10-75	-	-

Specification

- Connector
Aluminum
 - Powder coated
Black, RAL 9005, textured finish
 - Plain finish, matte shot-blasted
- Socket cap screws ISO 4672
Stainless steel
- Hex nuts DIN 985
Stainless steel
Self-locking via polyamide ring
- RoHS

Information

The clamping bore of tube connectors GN 241 is not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations z the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessories.

Accessory

- Construction Tubes GN 990 → Page 1835
- Adjustable Hand Levers GN 911
→ Page 1784

How to order

1 2 3 4

GN 241-V45-76-2-SW

1 s (d)

2 k

3 Identification no.

4 Finish