




**elesa**  
Original design TCC-SL / TCC-SL-VD



**2 Identification no.**

- 2 With 2 stainless steel socket cap screws ISO 4762



**1**

d <sub>1</sub> Bore	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	z Screw locations	Accessory Recom. hand levers GN 911.9 for z l <sub>4</sub>	
B 18	64,5	35,5	29	M6-18	44	63
B 30	94,5	53,5	42	M8-25	63	78

**Specification**

**Connector clamp**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -20 °C to +100 °C
- Color
  - SW - Black, RAL 9005, matte finish
  - GR - Gray, RAL 7040, matt finish
  - VDB - Blue, RAL 5005, matte finish
- FDA compliant material
- Visually detectable

**Socket cap screw ISO 4762**

Stainless steel AISI 304

**Hex nuts DIN 985**

Stainless steel AISI 304

Self-locking with polyamide ring

RoHS

**Accessory**

**Page**

GN 990 Construction Tubes (Aluminum / Stainless Steel)	QVX
GN 290 Adapter Bushings	QVX
GN 911.9 Adjustable Hand Levers	QVX

The tube connectors GN 242.9 have two clamping bores. They hold typical construction tubes with full surface contact over the entire cross-section of the bore.

At the screw locations z, the socket cap screws reduce the bore cross-section for clamping. Adapter bushings GN 290 can be used to reduce the bore cross-sections to smaller diameters.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911.9 listed in the table as accessories.

The plastic used in version VDB is made from blue, visually detectable and FDA-compliant plastic granulate as per FDA CFR.21 and EU 10/2011.

**see also...**

	Page
GN 242 Tube Connectors (Aluminum)	QVX

**Technical Information**

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**How to order**

**GN 242.9-B18-2-SW**

1	d
2	Identification no.
3	Color