



1.1

1.2

1.3

1.4

2.1

2.2

2.3

2.4

² d ₁	³ d ₂ Thread		³ d ₃ H7 Bore		d ₄	h ₁	h ₂	h ₃
50	M 8	M 10	B 8	B 10	18	25	20	15
63	M 10	M 12	B 10	B 12	20	30	24	18
80	M 16	-	B 12	B 16	25	36	29	22

Specification

Plastic, Polyamide (PA)

- Shock-resistant
- Black, matte
- Hub bushing
- Steel, blackened

RoHS

On request

- Without bore



KT

Knurled handwheels GN 226 are mainly used instead of star and hand knobs for light adjusting or clamping applications.

see also...

GN 534 Knurled Knobs (Plastic)

Page

QVX

Technical Information

Cross holes GN 110

ISO Fundamental Tolerances

Plastic Characteristics

QVX

QVX

QVX

Accessory

GN 226.1 Cover Disks

GN 826 Clamping Elements (for Adjustable Spindles)

QVX

QVX

How to order

GN 226-KT-50-M10

¹ Material

² d₁

³ d₂ (d₃)

