




- 3

Type
- S

Stepless adjustment
- T

Adjustment with 15° division (serration)
- 4

Identification no.
- 2

With 3 stainless steel socket cap screws DIN 912

d ₁ Bore	d ₂ Bore	b Swivel width	k ₁	k ₂	l ₁	l ₂	l ₃	m ₁	m ₂	z ₁ Screw locations	z ₂ Screw location	Accessory Recom. hand lever GN 911			
												for z ₁ l ₄	for z ₂ l ₄		
B 20	B 20	40	42,5	40	147	52	40	43	72	M8-25	M8-30	-	-	63	78
B 25	B 25	40	42,5	40	147	52	40	43	72	M8-25	M8-30	63	78	63	78
B 30	B 30	40	42,5	40	147	52	40	43	72	M8-25	M8-30	63	78	63	78
B 40	B 40	65	74	65	230	77,5	65	70	115	M10-50	M10-55	-	-	78	92
B 42	B 42	65	74	65	230	77,5	65	70	115	M10-50	M10-55	-	-	78	92
B 45	B 45	65	74	65	230	77,5	65	70	115	M10-50	M10-55	78	92	78	92
B 48	B 48	65	74	65	230	77,5	65	70	115	M10-50	M10-55	78	92	78	92
B 50	B 50	65	74	65	230	77,5	65	70	115	M10-50	M10-55	78	92	78	92

Specification

• Aluminum

- Powder coated

Black, RAL 9005, textured finish

- Plain, matte shot-blasted

● SW

○ BL

• Socket cap screws DIN 912

Stainless steel AISI 304

• Hex nuts DIN 985

Stainless steel AISI 304

Self-locking via polyamide ring

• Stainless Steel Characteristics → Page 2166

• RoHS

- Accessory
- Adjustable Hand Levers GN 911 → Page 1784

Information

Swivel clamp connector joints GN 288 are an assembly of swivel clamp connectors. GN 276 and GN 278. For the version with stepless adjustment (Type S) swivel clamp connectors with centering step are used.

Within the identical swivel width „b“, all bores „d₁ / d₂“ can be combined as required.

The clamping bores are mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations z₁, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessory.

see also...

• Construction Tubes GN 990 → Page 1835

How to order		1	d ₁
		2	d ₂
		3	Type
		4	Identification no.
		5	Finish

1

2

3

4

5

GN 288-B25-B25-S-2-BL