




													
d ₁ - d ₂ Bore - Bore	d ₁ - s ₂ Bore - Square	s ₁ - s ₂ Square - Square	b Swivel width	k	l ₁	l ₂	m	z ₁ Screw locations	z ₂ Screw location	Accessory Recom. hand lever GN 911 for z ₁ l ₃ for z ₂ l ₃			
B40-B40	B40-V40	V40-V40	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40-B42	B42-V40	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40-B45	B45-V40	V40-V45	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40-B48	B48-V40	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40-B50	B50-V40	V40-V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42-B42	B40-V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42-B45	B42-V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42-B48	B45-V45	V45-V45	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42-B50	B48-V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45-B45	B50-V45	V45-V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45-B48	B40-V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45-B50	B42-V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B48-B48	B45-V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B48-B50	B48-V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B50-B50	B50-V50	V50-V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92

Specification	
Connector clamp	
Aluminum	
• Powder coated	
Black, RAL 9005, textured finish	● SW
• Plain finish, matte shot-plasted	○ BL
Socket cap screws ISO 4762	
Stainless steel	
Hex nuts DIN 985	
Stainless steel	
Self-locking via polyamide ring	
RoHS	
Technical Information	Page
Stainless Steel Characteristics	QVX
Accessory	
GN 911 Adjustable Hand Levers	QVX

Swivel clamp connector joints GN 289 are an assembly of two swivel clamp connectors GN 279.

The square versions are also suitable for use with profile systems.

The clamping bores are not machined and are designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations z₁, the socket cap screws reduce the cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessory.

see also...	Page
GN 279 Swivel Clamp Connectors	QVX

How to order	1 d ₁ - s ₂ (d ₁ - d ₂ , s ₁ - s ₂)
	2 Type
	3 Identificaiton no.
	4 Finish
GN 289-B40-V40-S-2-BL	