




1		d ₁	d ₂	e	l ₁ ≈	l ₂	l ₃	l ₄	l ₅ min.	l ₆	A/F ₁	A/F ₂	A/F ₃	x Max. radial off-set	Max. pull / push load in kN
M	6	-	9,5	24,5	52	29	18,5	14	13	9,5	22	8	5	0,6	2,5
M	8	-	15	30	63	33	23,5	18	16	11,5	27	13	7	0,7	4,5
M	10	M 10 x 1,25	21	44	81	43	30,5	22	24	16	41	18	12	0,7	6,5
M	12	M 12 x 1,25	21	44	85	43	34,5	26	24	16	41	18	12	0,8	10
M	16	M 16 x 1,5	32	60	121	62	45	34	34	26	55	27	18	1	18
M	20	M 20 x 1,5	32	60	129	62	53	42	34	26	55	27	18	1	30

Specification

- Steel
 - Tempered
 - Phosphated
- Retaining ring (spring)
Stainless steel AISI 631
- RoHS

Information

Quick-fit couplings GN 240.2 have been designed to compensate a **radial** and **angular** off-set. Furthermore they are axially **freely** adjustable via the set screw.

A typical application is the axial link to a piston rod of a cylinder operating in any type of fixture or system.

The coupling is renowned by its very compact construction without any loose components.

The coupling is **not** designed for the transfer of torque.

see also...

- Quick-Fit Couplings GN 240
(with Radial Off-Set Compensation) → Page 1673

How to order

1

d₁

GN 240.2-M20x1,5