



<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub>	<sup>3</sup> l <sub>2</sub>						d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke
63	M 6	20	27	-	-	-	-	24	17,5	34,5	48,5	4
78	M 8	21	36	-	-	-	-	25	21	39,5	58,5	4
92	M 10	29	47	-	-	-	-	30	24	46,5	68,5	4
108	M 12	34	50	57	65	85	-	35	30	56,5	82	5

**Specification**

<sup>4</sup>

- Handle  
Zinc die casting
- Powder coated
  - Black, RAL 9005, textured finish ● **SW**
  - Black, RAL 9005, silk finish ● **SZ**
  - Orange, RAL 2004, textured finish ● **OS**
  - Red, RAL 3000, textured finish ● **RS**
  - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated ● **CR**
- Threaded stud and bushing  
Steel
  - Property class 5.8
  - Nitrided, blackened
- Retaining screw  
Steel, blackened
- *Strength Values of Screws → Page 2152*
- RoHS

**Information**

Adjustable hand levers GN 300.4 are produced with a clamping area which is linked via a thrust ball bearing (axial bearing) to the bushing and threaded stud of the hand lever. This has led to the following advantages:

- **Doubled** clamping force through vastly reduced friction.
- There is no movement on the contact area between adjustable handlever and component which greatly reduces any marking on the clamping area.
- In addition a reduced creep factor has been achieved by the increased preload.

How to order

<sup>1</sup>	l <sub>1</sub>
<sup>2</sup>	d <sub>1</sub>
<sup>3</sup>	l <sub>2</sub>
<sup>4</sup>	Color (Finish)

**GN 300.4-92-M10-47-RS**

