




1				2								
l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
22	M 3	M 4	M 5	-	-	8	10,5	18,5	2	16,5	3	5
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	22	3,5	9
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	22	3,5	9
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	28,5	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	34	4	14

Specification

1

2

3

- Handle
Zinc die casting
- Powder coated
 - Black, RAL 9005, textured finish
 - Orange, RAL 2004, textured finish
 - Red, RAL 3000, textured finish
 - Silver, RAL 9006, textured finish
- Bushing and retaining screw
Stainless steel AISI 303
- ISO Fundamental Tolerances → Page 2151
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- With inch threads

● SW

● OS

● RS

● SR

Information

Adjustable hand levers GN 302.1 have a straight lever, not inclined, being parallel to the clamping space.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Flat Adjustable Hand Levers GN 302 (Bushing Steel) → Page 448
- Adjustable Hand Levers GN 300 (Bushing Steel) → Page 428
- Adjustable Hand Levers GN 300.1 (Bushing Stainless Steel) → Page 438