



- 3 Identification no.**
- 2 With stainless steel socket cap screw DIN 912**

<b>1</b> $d_1$ Bore for clamping $\varnothing$		<b>2</b> $d_2$ Bore for sensor		<b>b</b> Swivel width	$d_3$	<b>k</b>	$l_1$	$l_2$	<b>m</b>	<b>t</b>	<b>z</b> Screw location	<b>Accessory</b> Recom. hand lever GN 911 for <b>z</b> $l_3$	
B 20	B 18	B 30	40	50	42,5	92	52	72	10	M8-25	-	-	
B 25	B 18	B 30	40	50	42,5	92	52	72	10	M8-25	63	78	
B 30	B 18	B 30	40	50	42,5	92	52	72	10	M8-25	63	78	

**Specification**

- Aluminum  
Powder coated  
Black, RAL 9005, textured finish **SW**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Adjustable Hand Levers GN 911  
→ Page 1784

**Information**

The clamping bore of sensor holders GN 276.4 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location **z**, the socket cap screw reduces the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by an adjustable hand lever GN 911 listed in the table as accessory.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Retaining Rods / Tubes GN 480.1* → Page 1833
- *Universal Work Holdings GN 177 (for Work Gripper Blocks GN 177.1)*  
→ Page 1806
- *Attachment Mounting Clamps GN 478* → Page 1795

**How to order**

<b>1</b> $d_1$
<b>2</b> $d_2$
<b>3</b> Identification no.
<b>4</b> Finish

**GN 276.4-B20-B18-2-SW**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9