




1			2			3						d3	d4	h1	h2	h3	h4
l1			d1			l2						d3	d4	h1	h2	h3	h4
30	M 3	-	6	8	10	12	16	-	-	-	-	10	13	26,5	4	31	3,5
30	M 4	-	12	16	20	25	32	-	-	-	-	10	13	26,5	4	31	3,5
30	M 5	M 6	12	16	20	25	32	40	50	-	-	10	13	26,5	4	31	3,5
45	M 4	-	12	16	20	25	32	-	-	-	-	10	13	26,5	4	35	3,5
45	M 5	M 6	12	16	20	25	32	40	50	-	-	10	13	26,5	4	35	3,5
63	M 6	M 8	12	16	20	25	32	40	50	63	13,5	17,5	32,5	6,5	45	4	
63	M 10	-	20	25	32	40	50	63	-	-	13,5	17,5	32,5	6,5	45	4	
78	M 8	M 10	16	20	25	32	40	50	63	80	16	21	37,5	8	55	4	

Specification

- Handle
 - Zinc die casting
- Powder coated
 - Black, RAL 9005
 - Textured finish
- Releasing button
 - Plastic
 - Black, RAL 9005
 - Orange, RAL 2004
 - Gray, RAL 7035
- Threaded stud
 - Stainless steel AISI 303
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- Handle in colors of GN 300

Information

Adjustable hand levers GN 303.1 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

The push button is a design element that offers an easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.

- see also...
- Adjustable Hand Levers GN 303.2 (with Push Button, Threaded Stud Steel) → Page 445

How to order		1	l1
		2	d1
		3	l2
		4	Color handle
		5	Color releasing button

GN 303.1-63-M8-32-SW-G

1

2

3

4

5