




Identification no. **1** (Size $d_1 = 18 \dots 50$)Identification no. **2** (Size $d_1 = 30 \dots 50$)Identification no. **1** and **2** (Size $d_1 = 60$)**3 Identification no.**

- 1** For mechanical position indicators
GN 953 / GN 954 / GN 955
- 2** For electronic position indicators
GN 9053 / GN 9054



d₁ Ø Linear actuator	d₂ H7 / f8	b	d₃	h	l₁		l₂	l₃	For position indicators
					Id. no. 1	Id. no. 2			
18	6	24	10	33	28	-	16	10	GN 955
30	8	35	14	42	35	42	15	10	GN 954 / GN 9054
40	12	47	20	56,5	39	49	16	10	GN 953 / GN 9053
50	12	58	20	61	39	49	17	10	GN 953 / GN 9053
60	14	64	20	-	44	49	18	-	GN 953 / GN 9053

Specification

- Adaptor shaft
Steel
Blackened
- Torque support
Aluminum
Black anodized
- ISO Fundamental Tolerances → Page 2151
- RoHS

Accessory

- Position indicators and handwheels have to be ordered separately.

On request

- Linear actuators with analog position indicator GN 000.8

Information

The GN 295 installation kits are needed for mounting a position indicator on linear units. The installation kits comprise an adapter shaft and a torque support including attachment screws.

Order mechanical position indicators GN 953 / GN 954 / GN 955 with a counter pitch that corresponds to that of the trapezoidal threaded spindle.

For position indicators GN 9053 / GN 9054, the position indicator pitch is programmed.

see also...

- Position Indicators GN 953 / GN 954 / GN 955 → Page 396 / 398 / 400
- Position Indicators GN 9053 / GN 9054 → Page 402 / 404
- Linear Actuators → Page 1950 ff.
- Drive / Transfer Units GN 391 → Page 1988

How to order**GN 295-30-8-1**

1	d₁
2	d₂
3	Identification no.